

166-90731

HellermannTyton

Article Number: 166-90731



Description: Liquid-Tight Metallic Conduit, Flexible, 0.75" (25mm) Dia, Galvanized Steel core w/Galvanized Inner Braid and PVC Cover, Black, 82ft/Reel

Base Data		
	Local Order Number	LTBRDP25B-25M
	Type	LTBRDP25B-25M
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Flexible metallic conduit provides liquid-tight performance to IP66 + IP67 + IP68 + IP69 when used with LTP or LTPUL fittings. • Helically wound (spiral) galvanized steel core with an interlocking design delivers high degree of compression strength and impact resistance. • Smooth PVC cover resists oil and grease and will not wrinkle or crack when conduit is bent; also provides corrosion resistance. • Center layer of galvanized steel overbraid provides EMC screening 60dB @ 1MHz. • Manufactured to UL360 requirements.
	Quantity Per	reel
	Product Description	A flexible, liquid-tight galvanized steel conduit with a smooth, oil-resistant PVC coating and galvanized steel middle braid. LTBRDP series conduit is designed for liquid-tight applications where a high degree of corrosion resistance is required along with EMC screening. Use with HelaGuard LTP or LTPUL series metallic fittings for IP66 + IP67 + IP68 + IP69 ratings.
	Technical Description	Manufacturer Reference Number: LTBRDP25B-25M
	Short Description	Liquid-Tight Metallic Conduit, Flexible, 0.75" (25mm) Dia, Galvanized Steel core w/Galvanized Inner Braid and PVC Cover, Black, 82ft/Reel
Product Dimensions		
	Length L (Imperial)	82.0ft
	Length L (Metric)	25.0m
	Reel Length (imperial)	82.0ft
	Diameter D (imperial)	0.83"
	Diameter D (metric)	21.0mm
	Outside Diameter D (imperial)	1.04"
	Outside Diameter OD (metric)	26.4mm
	Nominal Diameter (Imperial)	3/4"
	Nominal Diameter (Metric)	25.0mm
	Inside Bend Radius (Metric)	100mm

166-90731



Material and Specifications		
	Material	Galvanised Steel (GS)
	Material Shortcut	GS
	Flammability	Self-Extinguishing according to EN IEC 61386-1
	Operating Temperature	-4°F to +221°F (-20°C to +105°C)
Logistic and Packaging		
	Package Quantity (Imperial)	82ft
	Package Quantity (Metric)	25.0m
	Weight (imperial)	27.7lbs
	Weight (Metric)	12.58kg