

166-90742

HellermannTyton



Article Number: 166-90742

Description: HelaGuard M63 Fiber Sealing Washer, 63mm Dia, Vulcanized Fiber, Red, 10 pcs/pkg

Base Data		
	Local Order Number	FW63
	Type	FW63
	Color	Red (RD)
	Features and benefits	<ul style="list-style-type: none"> • Rugged, tough material (78 Shore D Hardness) for tighter seal. • Protects against water and dust. • For metric or NPT threads. • Resistant to oil.
	Quantity Per	pack
	Product Description	Vulcanized Fiber Sealing Washer used with metallic threaded fittings. Suitable for Metric or NPT threaded fittings.
	Short Description	HelaGuard M63 Fiber Sealing Washer, 63mm Dia, Vulcanized Fiber, Red, 10 pcs/pkg
Product Dimensions		
	Mounting Hole Diameter D (Metric)	63.0 mm
	Outside Diameter D (imperial)	2.87"
	Outside Diameter OD (metric)	73.0mm
	Nominal Diameter (Imperial)	2-1/2"
	Nominal Diameter (Metric)	63mm
	Wall Thickness WT (Metric)	1.6mm
Material and Specifications		
	Material	Vulcanised Fibre (VF)
	Material Shortcut	VF
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Logistic and Packaging		
	Package Quantity (Imperial)	10

166-90742



Logistic and
Packaging

Package Quantity (Metric)

10Pieces