

166-90769

HellermannTyton

Article Number: 166-90769



Description: Metallic Compression Fitting, Fixed Straight, M63 Metric Thread, 2" (63mm) Dia, NPB Metal, 1/pkg

Base Data		
	Local Order Number	FU63-M63-M
	Type	FU63-M63-M
	Color	Metal (ML)
	Features and benefits	<ul style="list-style-type: none"> • Nickel plated brass compression fitting used with FU-x series flexible metallic conduit. • Two part fitting comprised of shell and body with external metric thread delivers IP40 ingress protection. • Suitable for knockouts and secured with a metric threaded locknut.
	Quantity Per	pack
	Product Description	Two-part nickel plated brass straight fitting with fixed external metric thread. Fitting comprised of shell and body suitable for knockout entries. For use with FU-x flexible metal conduit.
	Technical Description	Manufacturer Reference Number: FU63-M63-M
	Short Description	Metallic Compression Fitting, Fixed Straight, M63 Metric Thread, 2" (63mm) Dia, NPB Metal, 1/pkg
Product Dimensions		
	Length L (Imperial)	1.97"
	Length L (Metric)	50.0mm
	Bore Diameter (Imperial)	2.13"
	Bore Diameter (Metric)	54.1mm
	Thread Length (Imperial)	0.71"
	Wrenching Flat Size (Imperial)	1.97"
	Wrenching Flat Size (Metric)	50.0mm
	Height H (Imperial)	2.76"
	Height H (Metric)	70.0mm
	Nominal Diameter (Imperial)	2-1/2"
	Nominal Diameter (Metric)	63mm
	Thread Length (metric)	18mm
	Thread Size (Metric)	M63

166-90769



Material and Specifications		
	Material	Nickel Plated Brass (NPB)
	Material Shortcut	NPB
	Operating Temperature	-58°F to +572°F (-50°C to +300°C)
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1Pack