

166-90772

# HellermannTyton

Article Number: 166-90772



Description: Metallic Compression Fitting, Straight, M16 Metric Thread, 5/16" (12mm) Dia, NPB Metal, 10/pkg

Base Data	
Local Order Number	FSU12-M16-C
Type	FSU12-M16-C
Color	Metal (ML)
Features and benefits	<ul style="list-style-type: none"> <li>Nickel plated brass compression fitting used with FSU, LFHU and FPU flexible metallic conduit.</li> <li>Fitting includes elastomeric sealing washer for IP65 ingress protection.</li> <li>Suitable for knockouts or NPT / Metric threaded entries as fitting rotates until tightened.</li> </ul>
Quantity Per	pack
Product Description	Multipart straight compression fitting with fixed external thread pattern suitable for threaded or knockout entries. Constructed with nickel plated brass components that resist corrosion, ensures high mechanical strength and electrical continuity. Fitting comprised of body, nut, grounding ferrule and nylon compression seal. For use with FSU, FPU, and LFHU flexible metal conduits.
Technical Description	Manufacturer Reference Number: FSU12-M16-C
Short Description	Metallic Compression Fitting, Straight, M16 Metric Thread, 5/16" (12mm) Dia, NPB Metal, 10/pkg
Product Dimensions	
Length L (Imperial)	1.17"
Length L (Metric)	29.8mm
Bore Diameter (Imperial)	0.34"
Bore Diameter (Metric)	8.6mm
Thread Length (Imperial)	0.39"
Wrenching Flat Size (Imperial)	0.78"
Wrenching Flat Size (Metric)	19.8mm
Height H (Imperial)	0.79"
Height H (Metric)	20.0mm
Nominal Diameter (Imperial)	5/16"
Nominal Diameter (Metric)	12.0mm

166-90772



Product Dimensions	Thread Length (metric)	10mm
	Thread Size (Metric)	M16
Material and Specifications		
	Material	Polyamide 6 (PA6)
	Material Shortcut	NPB
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces