

166-90773

Article Number: 166-90773



Description: Metallic Compression Fitting, Fixed Straight, M16 Metric Thread, 5/16" (12mm) Dia, NPB Metal, 10/pkg

Base Data	
Local Order Number	FSU12-M16-M
Type	FSU12-M16-M
Color	Metal (ML)
Features and benefits	<ul style="list-style-type: none"> <li>• Nickel plated brass compression fitting used with FSU, LFHU and FPU flexible metallic conduit.</li> <li>• Two part fitting comprised of shell and body with external metric thread delivers IP54 ingress protection.</li> <li>• Suitable for knockouts and secured with a metric threaded locknut.</li> </ul>
Quantity Per	pack
Product Description	Two-part nickel plated brass straight fitting with fixed external metric thread. Fitting comprised of shell and body suitable for knockout entries. For use with FSU, FPU and LFHU flexible metal conduit.
Technical Description	Manufacturer Reference Number: FSU12-M16-M
Short Description	Metallic Compression Fitting, Fixed Straight, M16 Metric Thread, 5/16" (12mm) Dia, NPB Metal, 10/pkg
Product Dimensions	
Length L (Imperial)	0.91"
Length L (Metric)	23.0mm
Bore Diameter (Imperial)	0.34"
Bore Diameter (Metric)	8.5mm
Thread Length (Imperial)	0.32"
Wrenching Flat Size (Imperial)	0.91"
Wrenching Flat Size (Metric)	23.0mm
Height H (Imperial)	0.67"
Height H (Metric)	17.0mm
Nominal Diameter (Imperial)	5/16"
Nominal Diameter (Metric)	12.0mm
Thread Length (metric)	8mm
Thread Size (Metric)	M16

166-90773



Material and Specifications		
	Material	Nickel Plated Brass (NPB)
	Material Shortcut	NPB
	Operating Temperature	-58°F to +572°F (-50°C to +300°C)
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces