

169-60021

HellermannTyton



Article Number: 169-60021

Description: Convoluted Tubing, Slit, 1" Dia, PA6, Black with Gray Stripe, 50ft/box

Base Data		
	Local Order Number	169-60021
	Type	CTN10
	Color	Black with Gray Stripe (BKSTGY)
	Features and benefits	<ul style="list-style-type: none"> • Durable tubing provides protection of wire harness from friction, vibration, fraying and puncture • Tubing protects cables and wires against automotive fluids, vibration wear • Weather resistant material provides protection against water, snow, ice, and the effects of heat, cold, and sunlight
	Quantity Per	box
	Product Description	HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.
	Technical Description	Convoluted Tubing, Slit, 1" Dia., PA6, Black w/Gray Stripe
	Short Description	Convoluted Tubing, Slit, 1" Dia, PA6, Black with Gray Stripe, 50ft/box
Product Dimensions		
	Length L (Imperial)	50.0ft
	Length L (Metric)	15.2m
	Inner Diameter D (Imperial)	1.06"
	Inner Diameter ID (metric)	26.92mm
	Diameter D (imperial)	1.32"
	Diameter D (metric)	33.53mm
	Diameter D2 (imperial)	1.06"
	Diameter D2 (metric)	26.92mm
	Outside Diameter D (imperial)	1.32"
	Outside Diameter OD (metric)	33.53mm
	Nominal Diameter (Imperial)	1"

169-60021



Product Dimensions	Nominal Diameter (Metric)	25.4mm
	Wall Thickness WT (Imperial)	.006"
	Wall Thickness WT (Metric)	0.152mm
Material and Specifications		
	Material	Polyamide 6 (PA6)
	Material Shortcut	PA6
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +300°F (-40°C to +149°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	50ft
	Package Quantity (Metric)	15.24m
	Customs Number(Schedule B)	3926909987