

169-60506

HellermannTyton



Article Number: 169-60506

Description: Convoluted Tubing, Slit, .5" Dia, PE, Black, 8500 ft/carton

Base Data		
	Local Order Number	CTP120
	Type	CTP120
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install • Tubing provides full coverage where spiral wrap or other coverings may not be suitable • In harsh applications the tubing can provide resistance to crushing, impact, and abrasion • Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires
	Quantity Per	carton
	Product Description	HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.
	Technical Description	Convoluted Tubing, Slit, 1/2" Dia., PE, Black
	Short Description	Convoluted Tubing, Slit, .5" Dia, PE, Black, 8500 ft/carton
Product Dimensions		
	Length L (Imperial)	8500.0ft
	Length L (Metric)	2590.8m
	Inner Diameter D (Imperial)	0.516"
	Inner Diameter ID (metric)	13.11mm
	Diameter D (imperial)	0.70"
	Diameter D (metric)	17.78mm
	Diameter D2 (imperial)	0.516"
	Diameter D2 (metric)	13.11mm
	Outside Diameter D (imperial)	0.70"

169-60506



Product Dimensions	Outside Diameter OD (metric)	17.78mm
	Nominal Diameter (Imperial)	1/2"
	Nominal Diameter (Metric)	12.70mm
	Wall Thickness WT (Imperial)	.005"
	Wall Thickness WT (Metric)	0.127mm
Material and Specifications		
	Material	Polyethylene (PE)
	Material Shortcut	PE
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +199°F (-40°C to +93°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	8500ft
	Package Quantity (Metric)	2590.8m
	Customs Number(Schedule B)	3926909987