

169-60533

HellermannTyton



Article Number: 169-60533

Description: Convoluted Tubing, Slit, .75" Dia, PE, Red, 550 ft/carton

Base Data		
	Local Order Number	169-60533
	Type	CTP340
	Color	Red (RD)
	Features and benefits	<ul style="list-style-type: none"> • Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install. • Tubing provides full coverage where spiral wrap or other coverings may not be suitable. • In harsh applications the tubing provides resistance to crushing, impact, and abrasion. • Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.
	Quantity Per	carton
	Product Description	HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.
	Short Description	Convoluted Tubing, Slit, .75" Dia, PE, Red, 550 ft/carton
Product Dimensions		
	Length L (Imperial)	550.0ft
	Length L (Metric)	167.6m
	Inner Diameter D (Imperial)	0.759"
	Inner Diameter ID (metric)	19.28mm
	Diameter D (imperial)	0.989"
	Diameter D (metric)	25.12mm
	Diameter D2 (imperial)	0.759"
	Diameter D2 (metric)	19.28mm
	Outside Diameter D (imperial)	0.989"
	Outside Diameter OD (metric)	25.12mm

169-60533



Product Dimensions	Nominal Diameter (Imperial)	3/4"
	Nominal Diameter (Metric)	19.05mm
	Wall Thickness WT (Imperial)	.005"
	Wall Thickness WT (Metric)	0.127mm
Material and Specifications		
	Material	Polyethylene (PE)
	Material Shortcut	PE
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +199°F (-40°C to +93°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	550ft
	Package Quantity (Metric)	167.6m
	Customs Number(Schedule B)	3926909987