

170-03011

HellermannTyton



Article Number: 170-03011

Description: Braided Sleeve, Expandable, Flame Retardant, 1.5" Dia, PET, Black, 40 ft/reel

Base Data		
	Local Order Number	170-03011
	Type	BSPFR1120
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Treated polyester material contains a combustion inhibitor for use in applications where flame retardancy is required. • Braided design allows sleeving to expand by 150% to accommodate variations in wire bundle and eases installation.
	Quantity Per	reel
	Product Description	A flame retardant woven (threaded) polyester sleeving that is resistant to cuts and abrasion, and contains a combustion inhibitor allowing it to achieve a UL and CSA flame resistance rating of VW-1. Contains white tracer thread for easy identification.
	Short Description	Braided Sleeve, Expandable, Flame Retardant, 1.5" Dia, PET, Black, 40 ft/reel
Product Dimensions		
	Length L (Imperial)	40.0ft
	Length L (Metric)	12.2m
	Reel Length (imperial)	40.0ft
	Bundle Diameter Min. (Imperial)	1.0"
	Bundle Diameter Min. (Metric)	25.4mm
	Bundle Diameter Max. (Imperial)	2.125"
	Bundle Diameter Max. (Metric)	53.9mm
	Nominal Diameter (Imperial)	1-1/2"
	Nominal Diameter (Metric)	38.1mm
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET
	Flammability	VW-1

170-03011



Material and Specifications	Operating Temperature	-94°F to +248°F (-70°C to +125°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	40ft
	Package Quantity (Metric)	12.19m
	Customs Number(Schedule B)	3926909987
	Weight (imperial)	0.79lbs
	Weight (Metric)	0.358kg