

170-03012

HellermannTyton



Article Number: 170-03012

Description: Braided Sleeve, Expandable, Fray Resistant, .5" Dia, PET, Black, 100 ft/reel

Base Data		
	Local Order Number	170-03012
	Type	BSPSC120
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Cuts with scissors without fraying ends enables field installations without need for hot knife. • Material construction offers excellent abrasion and cut-through protection as well as inertness to common chemicals and fungus. • Expands to 150% of easy installation and reduced assembly time requirements.
	Quantity Per	reel
	Product Description	A versatile and economical general purpose braided sleeving that resists fraying when cut with ordinary scissors.
	Short Description	Braided Sleeve, Expandable, Fray Resistant, .5" Dia, PET, Black, 100 ft/reel
Product Dimensions		
	Length L (Imperial)	100.0ft
	Length L (Metric)	30.48m
	Reel Length (imperial)	100.0ft
	Bundle Diameter Min. (Imperial)	0.25"
	Bundle Diameter Min. (Metric)	6.4mm
	Bundle Diameter Max. (Imperial)	0.75"
	Bundle Diameter Max. (Metric)	19.1mm
	Nominal Diameter (Imperial)	1/2"
	Nominal Diameter (Metric)	12.7mm
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET
	Flammability	UL 94 V0

170-03012



Material and Specifications	Operating Temperature	-94°F to +248°F (-70°C to +125°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100ft
	Package Quantity (Metric)	30.48m
	Customs Number(Schedule B)	3926909987
	Weight (imperial)	0.82lbs
	Weight (Metric)	0.37kg