

170-03016

# HellermannTyton



Article Number: 170-03016

Description: Braided Sleeve, Expandable, Fray Resistant, 1.5" Dia, PET, Black, 50 ft/reel

Base Data		
	Local Order Number	170-03016
	Type	BSPSC1120
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Cuts with scissors without fraying ends enables field installations without need for hot knife.</li> <li>• Material construction offers excellent abrasion and cut-through protection as well as inertness to common chemicals and fungus.</li> <li>• Expands to 150% of easy installation and reduced assembly time requirements.</li> </ul>
	Quantity Per	reel
	Product Description	A versatile and economical general purpose braided sleeving that resists fraying when cut with ordinary scissors.
	Short Description	Braided Sleeve, Expandable, Fray Resistant, 1.5" Dia, PET, Black, 50 ft/reel
Product Dimensions		
	Length L (Imperial)	50.0ft
	Length L (Metric)	15.2m
	Reel Length (imperial)	50.0ft
	Bundle Diameter Min. (Imperial)	1.25"
	Bundle Diameter Min. (Metric)	31.8mm
	Bundle Diameter Max. (Imperial)	2.0"
	Bundle Diameter Max. (Metric)	50.8mm
	Nominal Diameter (Imperial)	1-1/2"
	Nominal Diameter (Metric)	38.1mm
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET
	Flammability	UL 94 V0

170-03016



Material and Specifications	Operating Temperature	-94°F to +248°F (-70°C to +125°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	50ft
	Package Quantity (Metric)	15.24m
	Customs Number(Schedule B)	3926909987
	Weight (Metric)	0.42kg
	Weight (imperial)	0.925lbs