

170-03018

HellermannTyton



Article Number: 170-03018

Description: Braided Sleeve, Expandable, Fray Resistant, Flame Retardant, .75" Dia, PET, Black, 75 ft/reel

Base Data		
	Local Order Number	170-03018
	Type	BSSCFR340
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Increased braid density coverage provides higher level of abrasion resistance without losing flexibility. • Treated yarns extinguish quickly and reduces potential flame spread to surrounding components. • Cuts with ordinary scissors without fraying ends.
	Quantity Per	reel
	Product Description	Treated polyester yarns that can be cut with sharp scissors and provides flame retardant properties. Well suited for situations where access to a hot knife is either impractical or impossible. Contains white tracer thread for easy identification.
	Short Description	Braided Sleeve, Expandable, Fray Resistant, Flame Retardant, .75" Dia, PET, Black, 75 ft/reel
Product Dimensions		
	Length L (Imperial)	75.0ft
	Length L (Metric)	22.9m
	Reel Length (imperial)	75.0ft
	Bundle Diameter Min. (Imperial)	0.625"
	Bundle Diameter Min. (Metric)	15.9mm
	Bundle Diameter Max. (Imperial)	1.0"
	Bundle Diameter Max. (Metric)	25.4mm
	Nominal Diameter (Imperial)	3/4"
	Nominal Diameter (Metric)	19.1mm
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET

170-03018



Material and Specifications	Flammability	UL VW-1
	Operating Temperature	-94°F to +248°F (-70°C to +125°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	75ft
	Package Quantity (Metric)	22.86m
	Customs Number(Schedule B)	3926909987
	Weight (Metric)	0.38kg
	Weight (imperial)	0.83lbs