

170-03019

# HellermannTyton



Article Number: 170-03019

Description: Braided Sleeve, Expandable, Fray Resistant, Flame Retardant, 1" Dia, PET, Black, 50 ft/reel

Base Data		
	Local Order Number	170-03019
	Type	BSSCFR100
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Increased braid density coverage provides higher level of abrasion resistance without losing flexibility.</li> <li>• Treated yarns extinguish quickly and reduces potential flame spread to surrounding components.</li> <li>• Cuts with ordinary scissors without fraying ends.</li> </ul>
	Quantity Per	reel
	Product Description	Treated polyester yarns that can be cut with sharp scissors and provides flame retardant properties. Well suited for situations where access to a hot knife is either impractical or impossible. Contains white tracer thread for easy identification.
	Short Description	Braided Sleeve, Expandable, Fray Resistant, Flame Retardant, 1" Dia, PET, Black, 50 ft/reel
Product Dimensions		
	Length L (Imperial)	50.0ft
	Length L (Metric)	15.2m
	Reel Length (imperial)	50.0ft
	Bundle Diameter Min. (Imperial)	0.75"
	Bundle Diameter Min. (Metric)	19.1mm
	Bundle Diameter Max. (Imperial)	1.188"
	Bundle Diameter Max. (Metric)	30.2mm
	Diameter D (imperial)	1.0"
	Nominal Diameter (Imperial)	1"
	Nominal Diameter (Metric)	25.4mm
Material and Specifications		
	Material	Polyester (PET)

170-03019



Material and Specifications	Material Shortcut	PET
	Flammability	Mil-202
	Operating Temperature	-94°F to +248°F (-70°C to +125°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	50ft
	Package Quantity (Metric)	15.24m
	Customs Number(Schedule B)	3926909987
	Weight (imperial)	0.62lbs
	Weight (Metric)	0.28kg