

170-03059

HellermannTyton

Article Number: 170-03059



Description: Braided Sleeve, Resin Coated Fiberglass, .5" Dia, GF, Black, 50 ft/reel

Base Data		
	Local Order Number	170-03059
	Type	BSHTFG120
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • An extremely tough sleeving material which provides thermal protection up to 1,200°F. • Sturdy construction maintains its tight structure under extreme shaking, scraping, pressure and varying temperature conditions. • Cuts easily with ordinary scissors for easy application. • UL VW-1 flammability rating for use in conditions requiring a very high degree of flame resistance.
	Quantity Per	reel
	Product Description	An extremely high-temperature resistant sleeving designed to protect wires and cables subjected to continuous temperature variations, vibration, abrasion, and mechanical stress.
	Short Description	Braided Sleeve, Resin Coated Fiberglass, .5" Dia, GF, Black, 50 ft/reel
Product Dimensions		
	Length L (Imperial)	50.0ft
	Length L (Metric)	15.2m
	Reel Length (imperial)	50.0ft
	Bundle Diameter Max. (Imperial)	0.75"
	Bundle Diameter Max. (Metric)	19.1mm
	Nominal Diameter (Imperial)	1/2"
	Nominal Diameter (Metric)	12.7mm
Material and Specifications		
	Material	Glass Fiber (GF)
	Material Shortcut	GF
	Flammability	VW-1
	Operating Temperature	-94°F to +1202°F (-70°C to +650°C)

170-03059



Material and Specifications	ROHS Compliant	Yes
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	50ft
	Package Quantity (Metric)	15.24m
	Customs Number(Schedule B)	7019901000
	Weight (imperial)	2.4lbs
	Weight (Metric)	1.09kg