Article Number: 170-03063

Description: Braided Sleeving, Aluminum Laminated Fiberglass, .75" Dia, AL/GF, Silver 100 ft/reel

Base Data		
	Local Order Number	170-03063
	Type	BSHTTST34SR
	Color	Silver (SR)
	Features and benefits	• A layer of aluminum provides protection from chemicals, scraping, cuts and abrasion. • Additional layer also provides insulation barrier for vulnerable wires and cables within high temperature environments. • Cuts with ordinary scissors for fast, easy application.
	Product Description	A tubular shaped sleeving product that combines the protection of bonded aluminum and fiberglass into a single solution that is able to deflect radiant heat away from sensitive components inside the tube.
	Short Description	Braided Sleeving, Aluminum Laminated Fiberglass, .75" Dia, AL/GF, Silver 100 ft/reel
Product Dimensions		
	Length L (Imperial)	100.0ft
	Length L (Metric)	30.48m
	Reel Length (imperial)	100.0ft
	Bundle Diameter Max. (Imperial)	0.687"
	Bundle Diameter Max. (Metric)	17.5mm
	Nominal Diameter (Imperial)	3/4"
	Nominal Diameter (Metric)	19.1mm
Material and Specifications		
	Material	Aluminum (AL)
	Material Shortcut	GF
	Flammability	Non-Flammable
	Operating Temperature	-76°F to +491°F (-60°C to +255°C)
	ROHS Compliant	Yes

Logistic and Packaging		
	Package Quantity (Imperial)	100ft
	Package Quantity (Metric)	30.48m
	Customs Number(Schedule B)	7019901000
	Weight (Metric)	1.57kg
	Weight (imperial)	3.45lbs