

170-03074

# HellermannTyton

Article Number: 170-03074

Description: Braided Sleeving, Expandable, Flame Retardant, .75" Dia, PET, Gray, 75 ft/reel



Base Data		
	Local Order Number	170-03074
	Type	BSPFR348
	Color	Gray (GY)
	Features and benefits	<ul style="list-style-type: none"> <li>• Treated polyester material contains a combustion inhibitor for use in applications where flame retardancy is required.</li> <li>• Braided design allows sleeving to expand by 150% to accommodate variations in wire bundle and eases installation.</li> </ul>
	Quantity Per	reel
	Product Description	A flame retardant woven (threaded) polyester sleeving that is resistant to cuts and abrasion, and contains a combustion inhibitor allowing it to achieve a UL and CSA flame resistance rating of VW-1. Contains white tracer thread for easy identification.
	Short Description	Braided Sleeving, Expandable, Flame Retardant, .75" Dia, PET, Gray, 75 ft/reel
Product Dimensions		
	Length L (Imperial)	75.0ft
	Length L (Metric)	22.9m
	Reel Length (imperial)	75.0ft
	Bundle Diameter Min. (Imperial)	0.5"
	Bundle Diameter Min. (Metric)	12.7mm
	Bundle Diameter Max. (Imperial)	1.25"
	Bundle Diameter Max. (Metric)	31.8mm
	Nominal Diameter (Imperial)	3/4"
	Nominal Diameter (Metric)	19.1mm
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET
	Flammability	FAR 25

170-03074



Material and Specifications	Operating Temperature	-94°F to +248°F (-70°C to +125°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	75ft
	Package Quantity (Metric)	22.86m
	Customs Number(Schedule B)	3926909987
	Weight (imperial)	0.65lbs
	Weight (Metric)	0.3kg