

170-03078

HellermannTyton

Article Number: 170-03078

Description: Braided Sleeving, Expandable, .75" Dia, PET, Orange, 250 ft/bulk reel



Base Data		
	Local Order Number	170-03078
	Type	BSP343B
	Color	Orange (OG)
	Features and benefits	<ul style="list-style-type: none"> • Weave construction adjusts to twisting and flexing without creating wrinkles or bends. • Durable construction offers excellent abrasion and cut-through resistance as well as inertness to most chemicals and fungus. • Color options available to provide easy visual and safety identification of critical wiring components. • Expands to 150% of nominal diameter for fast, easy installation.
	Quantity Per	reel
	Product Description	General purpose expandable braided sleeving provides flexible abrasion protection for wire bundles and hoses.
	Short Description	Braided Sleeving, Expandable, .75" Dia, PET, Orange, 250 ft/bulk reel
Product Dimensions		
	Length L (Imperial)	250.0ft
	Length L (Metric)	76.2m
	Reel Length (imperial)	250.0ft
	Bundle Diameter Min. (Imperial)	0.5"
	Bundle Diameter Min. (Metric)	12.7mm
	Bundle Diameter Max. (Imperial)	1.25"
	Bundle Diameter Max. (Metric)	31.8mm
	Nominal Diameter (Imperial)	3/4"
	Nominal Diameter (Metric)	19.1mm
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET

170-03078



Material and Specifications	Flammability	FAR 25
	Halogenfree	Yes
	Operating Temperature	-94°F to +248°F (-70°C to +125°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	250ft
	Package Quantity (Metric)	76.2m
	Customs Number(Schedule B)	3926909987
	Weight (Metric)	1.36kg
	Weight (imperial)	3.0