

170-03082

HellermannTyton



Article Number: 170-03082

Description: Braided Sleeving, Split Wrap, .25" Dia, PET, Orange, 200 ft/bulk reel

Base Data		
	Local Order Number	170-03082
	Type	BSPSW143B
	Color	Orange (OG)
	Features and benefits	<ul style="list-style-type: none"> • Split wrap design installs quickly, saving assembly time and future accessibility without disassembly. • Unique construction retains shape and rigidity throughout unrolling. • Easy open design allows quick assembly, future access, and ability to apply protective sleeving post assembly or post installation situations.
	Quantity Per	box
	Product Description	A lateral split, semi-rigid and flame retardant braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires.
	Short Description	Braided Sleeving, Split Wrap, .25" Dia, PET, Orange, 200 ft/bulk reel
Product Dimensions		
	Length L (Imperial)	200.0ft
	Length L (Metric)	61.0m
	Reel Length (imperial)	200.0ft
	Bundle Diameter Max. (Imperial)	0.25"
	Bundle Diameter Max. (Metric)	6.4mm
	Nominal Diameter (Imperial)	1/4"
	Nominal Diameter (Metric)	6.4mm
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET
	Flammability	UL 94 V0
	Operating Temperature	-94°F to +248°F (-70°C to +125°C)

170-03082



Material and Specifications	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	200ft
	Package Quantity (Metric)	60.96m
	Customs Number(Schedule B)	3926909987
	Weight (imperial)	1.2lbs
	Weight (Metric)	0.54kg