

170-03089

# HellermannTyton



Article Number: 170-03089

Description: Braided Sleeve, Expandable, Flame Retardant, .125" Dia, PET, Black, 1000 ft/bulk reel

Base Data		
	Local Order Number	170-03089
	Type	BSPFR180B
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Treated polyester material contains a combustion inhibitor for use in applications where flame retardancy is required.</li> <li>• Braided design allows sleeving to expand by 150% to accommodate variations in wire bundle and eases installation.</li> </ul>
	Quantity Per	reel
	Product Description	A flame retardant woven (threaded) polyester sleeving that is resistant to cuts and abrasion, and contains a combustion inhibitor allowing it to achieve a UL and CSA flame resistance rating of VW-1. Contains white tracer thread for easy identification.
	Short Description	Braided Sleeve, Expandable, Flame Retardant, .125" Dia, PET, Black, 1000 ft/bulk reel
Product Dimensions		
	Length L (Imperial)	1000.0ft
	Length L (Metric)	304.8m
	Reel Length (imperial)	1000.0ft
	Bundle Diameter Min. (Imperial)	0.094"
	Bundle Diameter Min. (Metric)	2.4mm
	Bundle Diameter Max. (Imperial)	0.25"
	Bundle Diameter Max. (Metric)	6.4mm
	Nominal Diameter (Imperial)	1/8"
	Nominal Diameter (Metric)	3.2mm
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET
	Flammability	Mil-202

170-03089



Material and Specifications	Operating Temperature	-94°F to +248°F (-70°C to +125°C)
	ROHS Compliant	Yes
	Certification/Specification	UL94 VW-1
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1000ft
	Package Quantity (Metric)	304.8m
	Customs Number(Schedule B)	3926909987
	Weight (Metric)	0.73kg
	Weight (imperial)	1.6lbs