

170-03152

# HellermannTyton



Article Number: 170-03152

Description: Braided Sleeve, Hook &amp; Loop, 2.5" Dia, PET, Black, 100 ft/bulk reel

Base Data		
	Local Order Number	170-03152
	Type	BSHKLP212B
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Flexible construction that conforms to irregular shapes and contours.</li> <li>• Hook and loop feature wraps over cable bundle allowing future access to cables.</li> <li>• Easy access saves assembly time and allows for easy splicing or insertion of additional wires.</li> </ul>
	Quantity Per	reel
	Product Description	Expandable braided sleeving with hook & loop strip for wrapping around cable assemblies. Color matched hook & loop closure provides an easy on and off installation, as well as convenient access for harness break-outs.
	Short Description	Braided Sleeve, Hook & Loop, 2.5" Dia, PET, Black, 100 ft/bulk reel
Product Dimensions		
	Length L (Imperial)	100.0ft
	Length L (Metric)	30.48m
	Reel Length (imperial)	100.0ft
	Bundle Diameter Max. (Imperial)	2.5"
	Bundle Diameter Max. (Metric)	63.5mm
	Nominal Diameter (Imperial)	2-1/2"
	Nominal Diameter (Metric)	63.5mm
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET
	Flammability	UL 94 V0
	Operating Temperature	-94°F to +248°F (-70°C to +125°C)
	ROHS Compliant	Yes

170-03152



Material and Specifications	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100ft
	Package Quantity (Metric)	30.48m
	Customs Number(Schedule B)	3926909987
	Weight (Metric)	1.70kg
	Weight (imperial)	3.75lbs