

170-03162

HellermannTyton



Article Number: 170-03162

Description: Nomex(R) High Temperature Woven Sleeve, .75" Dia, GN, 100 ft/bulk reel

Base Data		
	Local Order Number	170-03162
	Type	BSNMX345B
	Color	Green (GN)
	Features and benefits	• Self extinguishing material does not melt and is unaffected by most acids, and provides excellent thermal stability against direct flame. • Meets FMVSS 302 specifications for use in automotive engineering. • Material cuts with ordinary scissors which reduces assembly time.
	Quantity Per	reel
	Product Description	A densely woven aramid fiber sleeve, this soft and flexible material is self extinguishing and can withstand temperatures reaching up to 662°F.
	Short Description	Nomex(R) High Temperature Woven Sleeve, .75" Dia, GN, 100 ft/bulk reel
Product Dimensions		
	Length L (Imperial)	100.0ft
	Length L (Metric)	30.48m
	Reel Length (imperial)	100.0ft
	Bundle Diameter Min. (Imperial)	0.56"
	Bundle Diameter Min. (Metric)	14.2mm
	Bundle Diameter Max. (Imperial)	1.0"
	Bundle Diameter Max. (Metric)	25.4mm
	Nominal Diameter (Imperial)	3/4"
	Nominal Diameter (Metric)	19.1mm
Material and Specifications		
	Material	Polyaramid Polymetaphenylene Isophthalamide
	Material Shortcut	NOMEX®
	Flammability	VW-1
	Operating Temperature	-320°F to +650°F (-196 °C to +350 °C)

170-03162



Material and Specifications	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100ft
	Package Quantity (Metric)	30.48m
	Customs Number(Schedule B)	3926909987
	Weight (imperial)	1.34lbs
	Weight (Metric)	0.61kg