

170-03165

Article Number: 170-03165

Description: Nomex(R) High Temperature Woven Sleeving, 1.5" Dia, GN, 100 ft/bulk reel



Base Data	Local Order Number	170-03165
	Type	BSNMX1125B
	Color	Green (GN)
	Features and benefits	<ul style="list-style-type: none"> • Self extinguishing material does not melt and is unaffected by most acids, and provides excellent thermal stability against direct flame. • Meets FMVSS 302 specifications for use in automotive engineering. • Material cuts with ordinary scissors which reduces assembly time.
	Quantity Per	reel
	Product Description	A densely woven aramid fiber sleeving, this soft and flexible material is self extinguishing and can withstand temperatures reaching up to 662°F.
	Short Description	Nomex(R) High Temperature Woven Sleeving, 1.5" Dia, GN, 100 ft/bulk reel
	Product Dimensions	Length L (Imperial)
Length L (Metric)		30.48m
Reel Length (imperial)		100.0ft
Bundle Diameter Min. (Imperial)		1.25"
Bundle Diameter Min. (Metric)		31.8mm
Bundle Diameter Max. (Imperial)		1.75"
Bundle Diameter Max. (Metric)		44.4mm
Nominal Diameter (Imperial)		1-1/2"
Nominal Diameter (Metric)		38.1mm
Material and Specifications	Material	Polyaramid Polymetaphenylene Isophthalamide
	Material Shortcut	NOMEX®
	Flammability	VW-1
	Operating Temperature	-320°F to +650°F (-196 °C to +350 °C)

170-03165



Material and Specifications	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100ft
	Package Quantity (Metric)	30.48m
	Customs Number(Schedule B)	3926909987
	Weight (imperial)	4.03lbs
	Weight (Metric)	1.83kg