

170-03180



Article Number: 170-03180

Description: Braided Sleeving, Expandable, Splice Free, .25" Dia, PET, Black, 1000 ft/bulk reel



Base Data		
	Local Order Number	170-03180
	Type	BSP140BSF
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"><li>• Weave construction adjusts to twisting and flexing without creating wrinkles or bends.</li><li>• Durable construction offers excellent abrasion and cut-through resistance as well as inertness to most chemicals and fungus.</li><li>• Color options available to provide easy visual and safety identification of critical wiring components.</li><li>• Expands to 150% of nominal diameter for fast, easy installation.</li></ul>
	Quantity Per	reel
	Product Description	General purpose expandable braided sleeving provides flexible abrasion protection for wire bundles and hoses.
	Short Description	Braided Sleeving, Expandable, Splice Free, .25" Dia, PET, Black, 1000 ft/bulk reel
Product Dimensions		
	Length L (Imperial)	1000.0ft
	Reel Length (imperial)	1000.0ft
	Nominal Diameter (Imperial)	1/4"
	Nominal Diameter (Metric)	6.35mm
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET
	Flammability	FMVSS 302
	Halogenfree	Yes
	Operating Temperature	-94°F to +248°F (-70°C to +125°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes

170-03180



Logistic and Packaging		
	Package Quantity (Imperial)	1000ft
	Package Quantity (Metric)	304.8m
	Customs Number(Schedule B)	3926909987