

170-03187

# HellermannTyton



Article Number: 170-03187

Description: Braided Sleeving, Expandable, Flame Retardant, .38" Dia, PET, Black, 500 ft/reel

Base Data		
	Local Order Number	170-03187
	Type	BSPFR380
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Treated polyester material contains a combustion inhibitor for use in applications where flame retardancy is required.</li> <li>• Braided design allows sleeving to expand by 150% to accommodate variations in wire bundle and eases installation.</li> </ul>
	Quantity Per	box
	Product Description	A flame retardant woven (threaded) polyester sleeving that is resistant to cuts and abrasion, and contains a combustion inhibitor allowing it to achieve a UL and CSA flame resistance rating of VW-1. Contains white tracer thread for easy identification.
	Short Description	Braided Sleeving, Expandable, Flame Retardant, .38" Dia, PET, Black, 500 ft/reel
Product Dimensions		
	Length L (Imperial)	500.0ft
	Length L (Metric)	152.4m
	Reel Length (imperial)	500.0ft
	Bundle Diameter Min. (Imperial)	0.188"
	Bundle Diameter Min. (Metric)	4.8mm
	Bundle Diameter Max. (Imperial)	0.5"
	Bundle Diameter Max. (Metric)	12.7mm
	Diameter D (imperial)	0.375"
	Diameter D (metric)	9.53mm
	Nominal Diameter (Imperial)	3/8"
	Nominal Diameter (Metric)	9.5mm
Material and Specifications		
	Material	Polyester (PET)

170-03187



Material and Specifications	Material Shortcut	PET
	Flammability	FMVSS 302
	Operating Temperature	-94°F to +248°F (-70°C to +125°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500ft
	Package Quantity (Metric)	152.4m
	Customs Number(Schedule B)	3926909987