

170-03189



Article Number: 170-03189

Description: Braided Sleeving, Split Wrap, 2" Dia, PET, White, 50 ft/bulk reel



| | | |
|-----------------------------|-------------------------------|--|
| Base Data | | |
| | Local Order Number | 170-03189 |
| | Type | BSPSW2010B |
| | Color | White (WH) |
| | Features and benefits | <ul style="list-style-type: none">• Split wrap design installs quickly, saving assembly time and future accessibility without disassembly.• Unique construction retains shape and rigidity throughout unrolling.• Easy open design allows quick assembly, future access, and ability to apply protective sleeving post assembly or post installation situations. |
| | Quantity Per | box |
| | Product Description | A lateral split, semi-rigid and flame retardant braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires. |
| | Short Description | Braided Sleeving, Split Wrap, 2" Dia, PET, White, 50 ft/bulk reel |
| Product Dimensions | | |
| | Length L (Imperial) | 50.0ft |
| | Reel Length (imperial) | 50.0ft |
| Material and Specifications | | |
| | Material | Polyester (PET) |
| | Material Shortcut | PET |
| | Flammability | UL 94 V0 |
| | Operating Temperature | -94°F to +248°F (-70°C to +125°C) |
| | ROHS Compliant | Yes |
| | UL Recognized (US and Canada) | Yes |

170-03189



| | | |
|------------------------|-----------------------------|--------|
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 50ft |
| | Package Quantity (Metric) | 15.24m |