

170-03210



Article Number: 170-03210

Description: Braided Sleeving, Expandable, .62" Dia, PA66 Monofilament, Black, 100 ft/reel



Base Data		
	Local Order Number	170-03210
	Type	BSPA66580
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Nylon monofilament construction weave offers a tight, 12 mil braid that provides full coverage but will not rot or retain moisture.</li> <li>• Material performs well in wet applications and where abiding substrate has a smooth surface.</li> </ul>
	Quantity Per	box
	Product Description	A pliable yet durable nylon sleeve that protects against cuts, abrasion and excessive wear caused by repetitive motion.
	Short Description	Braided Sleeving, Expandable, .62" Dia, PA66 Monofilament, Black, 100 ft/reel
Product Dimensions		
	Length L (Imperial)	100.0ft
	Length L (Metric)	30.48m
	Reel Length (imperial)	100.0ft
	Diameter D (imperial)	0.625"
	Diameter D (metric)	15.88mm
	Nominal Diameter (Imperial)	5/8"
	Nominal Diameter (Metric)	15.88mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	Non-Flammable
	Operating Temperature	-49°F to +302°F (-45°C to +150°C)
	ROHS Compliant	Yes

170-03210



Logistic and Packaging		
	Package Quantity (Imperial)	100ft
	Package Quantity (Metric)	30.48m
	Customs Number(Schedule B)	3926909987