

181-00214



Article Number: 181-00214

Description: Slotted Cable and Wiring Duct, 2.5" x 3", Adhesive, PVC, Gray, 120 ft/carton

Base Data	Local Order Number	181-00214
	Type	SLA2.5X3
	Color	Gray (GY)
	Features and benefits	<ul style="list-style-type: none"> <li>• Strong fingers prevent unwanted breaking.</li> <li>• Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct.</li> <li>• Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.</li> </ul>
	Quantity Per	carton
	Product Description	Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a wider opening is required. The lower score line allows the sidewall to be smoothly cut for joints and "T's".
	Technical Description	Adhesive
	Short Description	Slotted Cable and Wiring Duct, 2.5" x 3", Adhesive, PVC, Gray, 120 ft/carton
	Product Dimensions	Length L (Imperial)
Length L (Metric)		1.83m
Width W (Imperial)		2.5"
Width W (Metric)		63.5mm
Width W2 (Imperial)		2.5"
Width W2 (Metric)		63.5mm
Width W3 (Imperial)		0.4"
Width W3 (Metric)		10.2mm
Width W4 (imperial)		1.0"
Width W4 (metric)		25.4mm
Width W5 (imperial)		2.6"
Width W5 (metric)		66.0mm

181-00214



Product Dimensions	Width W6 (imperial)	0.75"
	Width W6 (metric)	19.05mm
	Height H (Imperial)	3.07"
	Height H (Metric)	77.90mm
	Mounting Hole Centers (Imperial)	4.0"
Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	Self-Extinguishing
	Operating Temperature	+122°F (+50°C)
	ROHS Compliant	Yes
	Certification/Specification	CSA
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	120ft
	Package Quantity (Metric)	36.6m