

181-00215

HellermannTyton



Article Number: 181-00215

Description: Slotted Cable and Wiring Duct, 2.5" x 3", Adhesive, PVC, Gray, 30ft/box

Base Data		
	Local Order Number	181-00215
	Type	SLA2.5X3
	Color	Gray (GY)
	Features and benefits	<ul style="list-style-type: none"> • Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.
	Quantity Per	box
	Product Description	Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a wider opening is required. The lower score line allows the sidewall to be smoothly cut for joints and "T's".
	Technical Description	Adhesive
	Short Description	Slotted Cable and Wiring Duct, 2.5" x 3", Adhesive, PVC, Gray, 30ft/box
Product Dimensions		
	Length L (Imperial)	6.0ft
	Length L (Metric)	1.83m
	Width W (Imperial)	2.5"
	Width W (Metric)	63.5mm
	Width W2 (Imperial)	2.5"
	Width W2 (Metric)	63.5mm
	Width W3 (Imperial)	0.4"
	Width W3 (Metric)	10.2mm
	Width W4 (imperial)	1.0"
	Width W4 (metric)	25.4mm
	Width W5 (imperial)	2.6"
	Width W5 (metric)	66.0mm

181-00215

HellermannTyton

Product Dimensions	Width W6 (imperial)	0.75"
	Width W6 (metric)	19.05mm
	Height H (Imperial)	3.07"
	Height H (Metric)	77.9mm
	Mounting Hole Centers (Imperial)	4.0"
Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	Self-Extinguishing
	Operating Temperature	+122°F (+50°C)
	ROHS Compliant	Yes
	Certification/Specification	CSA
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	30.0ft
	Package Quantity (Metric)	9.1m
	Customs Number(Schedule B)	3925900000