

181-00223

# HellermannTyton



Article Number: 181-00223

Description: Solid Cable and Wiring Duct, 2.5" x 3", Adhesive, PVC, Gray, 30ft/box

|                    |                                  |  |
|--------------------|----------------------------------|--|
| Base Data          |                                  |  |
|                    | Local Order Number               | 181-00223  |
|                    | Type                             | SDA2.5X3   |
|                    | Color                            | Gray (GY)  |
|                    | Features and benefits            | <ul style="list-style-type: none"> <li>• A temporary film is applied to the covers to protect against scratches and is writable for identification during installation.</li> <li>• Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement.</li> <li>• Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off. (Covers to be purchased separately)</li> </ul> |
|                    | Quantity Per                     | box  |
|                    | Product Description              | HellermannTyton's Pro-Duct, Solid Wall wiring duct efficiently routes and protects wire and cable. Solid Wall wiring duct it designed for straight wire runs where break outs are not required. Pro-Duct, Solid Wall wiring duct is manufactured from high impact, rigid PVC, comes in standard colors of white, gray and black, and is available in 6 foot lengths.   |
|                    | Technical Description            | Adhesive   |
|                    | Short Description                | Solid Cable and Wiring Duct, 2.5" x 3", Adhesive, PVC, Gray, 30ft/box  |
| Product Dimensions |                                  |  |
|                    | Length L (Imperial)              | 6.0ft  |
|                    | Length L (Metric)                | 1.83m  |
|                    | Width W (Imperial)               | 2.5"   |
|                    | Width W (Metric)                 | 63.5mm   |
|                    | Width W2 (Imperial)              | 2.5"   |
|                    | Width W2 (Metric)                | 63.5mm   |
|                    | Width W6 (imperial)              | 0.75"  |
|                    | Width W6 (metric)                | 19.05mm  |
|                    | Height H (Imperial)              | 3.07"  |
|                    | Height H (Metric)                | 77.9mm   |
|                    | Mounting Hole Centers (Imperial) | 4.0"   |

181-00223



|                             |                             |                         |
|-----------------------------|-----------------------------|-------------------------|
| Material and Specifications |                             |                         |
|                             | Material                    | Polyvinylchloride (PVC) |
|                             | Material Shortcut           | PVC                     |
|                             | Flammability                | Self-Extinguishing      |
|                             | Operating Temperature       | +122°F (+50°C)          |
|                             | ROHS Compliant              | Yes                     |
|                             | Certification/Specification | UL                      |
|                             | UL Recognized (US)          | Yes                     |
| Logistic and Packaging      |                             |                         |
|                             | Package Quantity (Imperial) | 30.0ft                  |
|                             | Package Quantity (Metric)   | 9.1m                    |
|                             | Customs Number(Schedule B)  | 3925900000              |