

181-00311

HellermannTyton

Article Number: 181-00311

Description: Wiring Duct Cover for 2 1/2" Duct, 6 ft Long, PVC, Black, 120 ft/carton



| | | |
|-----------------------------|-----------------------|--|
| Base Data | | |
| | Local Order Number | 181-00311 |
| | Type | TC2.5 |
| | Color | Black (BK) |
| | Features and benefits | <ul style="list-style-type: none"> • A temporary film is applied to the covers to protect against scratches and is writable for identification during installation. • Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement. • Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off. (Covers to be purchased separately) |
| | Quantity Per | carton |
| | Product Description | HellermannTyton's Pro-Duct wiring duct covers are sold separately and interchangeable among the 3 styles of duct (solid, slotted and high density). Manufactured from high impact, rigid PVC, Pro-Duct covers come in standard colors of white, gray and black. Wiring duct covers are available in 6 foot lengths. |
| | Technical Description | Wiring Duct Cover for 2 1/2" Duct, Black |
| | Short Description | Wiring Duct Cover for 2 1/2" Duct, 6 ft Long, PVC, Black, 120 ft/carton |
| Product Dimensions | | |
| | Length L (Imperial) | 6.0ft |
| | Length L (Metric) | 1.83m |
| | Width W (Imperial) | 2.5" |
| | Width W (Metric) | 63.5mm |
| Material and Specifications | | |
| | Material | Polyvinylchloride (PVC) |
| | Material Shortcut | PVC |
| | Flammability | Self-Extinguishing |
| | Operating Temperature | +122°F (+50°C) |
| | ROHS Compliant | Yes |

181-00311



| | | |
|-----------------------------|-----------------------------|-------|
| Material and Specifications | UL Recognized (US) | Yes |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 120ft |
| | Package Quantity (Metric) | 36.6m |