

181-00459

# HellermannTyton



Article Number: 181-00459

Description: Solid Cable and Wiring Duct, 1" x 3", Non-Adhesive, PVC, Black, 120 ft/carton

Base Data		
	Local Order Number	181-00459
	Type	SD1X3
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• A temporary film is applied to the covers to protect against scratches and is writable for identification during installation.</li> <li>• Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement.</li> <li>• Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off. (Covers to be purchased separately)</li> </ul>
	Quantity Per	carton
	Product Description	HellermannTyton's Pro-Duct solid wall wiring duct efficiently routes and protects wires and cables. Solid wall wiring duct is designed for straight wire runs where breakouts are not required. Pro-Duct solid wall wiring duct is manufactured from high-impact, rigid PVC, and is available in 6-foot lengths in standard colors of white, gray and black.
	Technical Description	Non-Adhesive
	Short Description	Solid Cable and Wiring Duct, 1" x 3", Non-Adhesive, PVC, Black, 120 ft/carton
Product Dimensions		
	Length L (Imperial)	6.0ft
	Length L (Metric)	1.83m
	Width W (Imperial)	1.0"
	Width W (Metric)	25.4mm
	Width W2 (Imperial)	1.0"
	Width W2 (Metric)	25.4mm
	Height H (Imperial)	3.07"
	Height H (Metric)	77.90mm
	Mounting Hole Centers (Imperial)	4.0"

181-00459



Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	Self-Extinguishing
	Operating Temperature	+122°F (+50°C)
	ROHS Compliant	Yes
	Certification/Specification	UL
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	120ft
	Package Quantity (Metric)	36.6m