

181-00469

# HellermannTyton



Article Number: 181-00469

Description: Solid Cable and Wiring Duct, 2" x 4", Non-Adhesive, PVC, Black, 120 ft/carton

|                    |                                  |  |
|--------------------|----------------------------------|--|
| Base Data          |                                  |  |
|                    | Local Order Number               | 181-00469  |
|                    | Type                             | SD2X4  |
|                    | Color                            | Black (BK)   |
|                    | Features and benefits            | <ul style="list-style-type: none"> <li>• A temporary film is applied to the covers to protect against scratches and is writable for identification during installation.</li> <li>• Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement.</li> <li>• Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off. (Covers to be purchased separately)</li> </ul> |
|                    | Quantity Per                     | carton   |
|                    | Product Description              | HellermannTyton's Pro-Duct, Solid Wall wiring duct efficiently routes and protects wire and cable. Solid Wall wiring duct is designed for straight wire runs where break outs are not required. Pro-Duct, Solid Wall wiring duct is manufactured from high impact, rigid PVC, comes in standard colors of white, gray and black, and is available in 6 foot lengths.   |
|                    | Technical Description            | Non-Adhesive   |
|                    | Short Description                | Solid Cable and Wiring Duct, 2" x 4", Non-Adhesive, PVC, Black, 120 ft/carton  |
| Product Dimensions |                                  |  |
|                    | Length L (Imperial)              | 6.0ft  |
|                    | Length L (Metric)                | 1.83m  |
|                    | Width W (Imperial)               | 2.0"   |
|                    | Width W (Metric)                 | 50.8mm   |
|                    | Width W2 (Imperial)              | 2.0"   |
|                    | Width W2 (Metric)                | 50.8mm   |
|                    | Width W6 (imperial)              | 0.5"   |
|                    | Width W6 (metric)                | 12.7mm   |
|                    | Height H (Imperial)              | 4.07"  |
|                    | Height H (Metric)                | 103.40mm   |
|                    | Mounting Hole Centers (Imperial) | 4.0"   |

181-00469



|                             |                             |                         |
|-----------------------------|-----------------------------|-------------------------|
| Material and Specifications |                             |                         |
|                             | Material                    | Polyvinylchloride (PVC) |
|                             | Material Shortcut           | PVC                     |
|                             | Flammability                | Self-Extinguishing      |
|                             | Operating Temperature       | +122°F (+50°C)          |
|                             | ROHS Compliant              | Yes                     |
|                             | Certification/Specification | UL                      |
|                             | UL Recognized (US)          | Yes                     |
| Logistic and Packaging      |                             |                         |
|                             | Package Quantity (Imperial) | 120ft                   |
|                             | Package Quantity (Metric)   | 36.6m                   |