

181-00480

HellermannTyton



Article Number: 181-00480

Description: Solid Cable and Wiring Duct, 8" x 4", Non-Adhesive, PVC, Black, 30 ft/ctn

Base Data		
	Local Order Number	181-00480
	Type	SD8X4
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • A temporary film is applied to the covers to protect against scratches and is writable for identification during installation. • Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement. • Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off. (Covers to be purchased separately)
	Quantity Per	carton
	Product Description	HellermannTyton's Pro-Duct, Solid Wall wiring duct efficiently routes and protects wire and cable. Solid Wall wiring duct it designed for straight wire runs where break outs are not required. Pro-Duct, Solid Wall wiring duct is manufactured from high impact, rigid PVC, comes in standard colors of white, gray and black, and is available in 6 foot lengths.
	Technical Description	Non-Adhesive
	Short Description	Solid Cable and Wiring Duct, 8" x 4", Non-Adhesive, PVC, Black, 30 ft/ctn
Product Dimensions		
	Length L (Imperial)	6.0ft
	Length L (Metric)	1.83m
	Width W (Imperial)	8.0"
	Width W (Metric)	203.2mm
	Width W2 (Imperial)	8.0"
	Width W2 (Metric)	203.2mm
	Height H (Imperial)	4.07"
	Height H (Metric)	103.40mm
	Mounting Hole Centers (Imperial)	4.0"

181-00480



Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	Self-Extinguishing
	Operating Temperature	+122°F (+50°C)
	ROHS Compliant	Yes
	Certification/Specification	UL
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	30ft
	Package Quantity (Metric)	9.14m