

181-00560

HellermannTyton



Article Number: 181-00560

Description: Slotted Cable and Wiring Duct, 3" x 5", Non-Adhesive, PVC, White, 120 ft/carton

Base Data		
	Local Order Number	181-00560
	Type	SL3X5
	Color	White (WH)
	Features and benefits	<ul style="list-style-type: none"> • Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.
	Quantity Per	carton
	Product Description	Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a wider opening is required. The lower score line allows the sidewall to be smoothly cut for joints and "T's".
	Technical Description	Non-Adhesive
	Short Description	Slotted Cable and Wiring Duct, 3" x 5", Non-Adhesive, PVC, White, 120 ft/carton
Product Dimensions		
	Length L (Imperial)	6.0ft
	Length L (Metric)	1.83m
	Width W (Imperial)	3.0"
	Width W (Metric)	76.2mm
	Width W2 (Imperial)	3.0"
	Width W2 (Metric)	76.2mm
	Width W3 (Imperial)	0.4"
	Width W3 (Metric)	10.2mm
	Width W4 (imperial)	1.0"
	Width W4 (metric)	25.4mm
	Width W5 (imperial)	4.6"
	Width W5 (metric)	116.8mm

181-00560

HellermannTyton

Product Dimensions	Width W6 (imperial)	1.0"
	Width W6 (metric)	25.4mm
	Height H (Imperial)	5.06"
	Height H (Metric)	128.50mm
	Mounting Hole Centers (Imperial)	4.0"
Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	Self-Extinguishing
	Operating Temperature	+122°F (+50°C)
	ROHS Compliant	Yes
	Certification/Specification	UL
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	120ft
	Package Quantity (Metric)	36.6m
	Customs Number(Schedule B)	3925900000