

181-00670

HellermannTyton

Article Number: 181-00670

Description: Slotted Cable and Wiring Duct, High-Density, 4" x 5", Adhesive, PVC, Gray, 60 ft/carton



Base Data		
	Local Order Number	181-00670
	Type	SLDHA4X5
	Color	Gray (GY)
	Features and benefits	<ul style="list-style-type: none"> • Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance. • Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation. • Mounting holes are uniform in size to the solid and slotted wall duct, but are offered every 2 inches to accommodate compact designs and ease installation.
	Quantity Per	carton
	Product Description	Pro-Duct high density, slotted wall, wiring duct features narrow fingers, equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.
	Technical Description	Adhesive
	Short Description	Slotted Cable and Wiring Duct, High-Density, 4" x 5", Adhesive, PVC, Gray, 60 ft/carton
Product Dimensions		
	Length L (Imperial)	6.0ft
	Length L (Metric)	1.83m
	Width W (Imperial)	4.0"
	Width W (Metric)	101.6mm
	Width W2 (Imperial)	4.0"
	Width W2 (Metric)	101.6mm
	Width W3 (Imperial)	0.16"
	Width W3 (Metric)	4.1mm
	Width W4 (imperial)	0.4"
	Width W4 (metric)	10.2mm
	Width W5 (imperial)	4.6"
	Width W5 (metric)	116.8mm

181-00670



Product Dimensions	Width W6 (imperial)	1.5"
	Width W6 (metric)	38.1mm
	Height H (Imperial)	5.07"
	Height H (Metric)	128.80mm
	Mounting Hole Centers (Imperial)	2.0"
Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	Self-Extinguishing
	Operating Temperature	+122°F (+50°C)
	ROHS Compliant	Yes
	Certification/Specification	CSA
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	60ft
	Package Quantity (Metric)	18.3m