

181-05503

HellermannTyton

Article Number: 181-05503

Description: Solid Cable and Wiring Duct, .5" x .5", Non-Adhesive, PVC, White, 30 ft/ctn



Base Data		
	Local Order Number	181-05503
	Type	SD.5X.5
	Color	White (WH)
	Features and benefits	<ul style="list-style-type: none"> • A temporary film is applied to the covers to protect against scratches and is writable for identification during installation. • Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement. • Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off. (Covers to be purchased separately)
	Quantity Per	box
	Product Description	HellermannTyton's Pro-Duct, Solid Wall wiring duct efficiently routes and protects wire and cable. Solid Wall wiring duct is designed for straight wire runs where break outs are not required. Pro-Duct, Solid Wall wiring duct is manufactured from high impact, rigid PVC, comes in standard colors of white, gray and black, and is available in 6 foot lengths.
	Technical Description	Non-Adhesive
	Short Description	Solid Cable and Wiring Duct, .5" x .5", Non-Adhesive, PVC, White, 30 ft/ctn
Product Dimensions		
	Length L (Imperial)	6.0ft
	Length L (Metric)	1.83m
	Width W (Imperial)	0.5"
	Width W (Metric)	12.7mm
	Width W2 (Imperial)	0.76"
	Width W2 (Metric)	19.3mm
	Height H (Imperial)	.55"
	Height H (Metric)	14.0mm
	Mounting Hole Centers (Imperial)	4.0"

181-05503



Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	Self-Extinguishing
	Operating Temperature	+122°F (+50°C)
	ROHS Compliant	Yes
	Certification/Specification	UL
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	30ft
	Package Quantity (Metric)	9.14m
	Customs Number(Schedule B)	3925900000