

181-14001



Article Number: 181-14001

Description: Slotted Cable and Wiring Duct, 1" x 4", Non-Adhesive, PVC, Black, 120 ft/carton

Base Data	
Local Order Number	181-14001
Type	SL1X4
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> <li>• Strong fingers prevent unwanted breaking.</li> <li>• Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct.</li> <li>• Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.</li> </ul>
Quantity Per	carton
Product Description	Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a wider opening is required. The lower score line allows the sidewall to be smoothly cut for joints and "T's".
Technical Description	Non-Adhesive
Short Description	Slotted Cable and Wiring Duct, 1" x 4", Non-Adhesive, PVC, Black, 120 ft/carton
Product Dimensions	
Length L (Imperial)	6.0ft
Length L (Metric)	1.83m
Width W (Imperial)	1.0"
Width W (Metric)	25.4mm
Width W2 (Imperial)	1.0"
Width W2 (Metric)	25.4mm
Width W3 (Imperial)	0.4"
Width W3 (Metric)	10.2mm
Width W4 (imperial)	1.0"
Width W4 (metric)	25.4mm
Width W5 (imperial)	3.6"
Width W5 (metric)	91.4mm

181-14001



Product Dimensions	Height H (Imperial)	4.07"
	Height H (Metric)	103.40mm
	Mounting Hole Centers (Imperial)	4.0"
Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	Self-Extinguishing
	Operating Temperature	+122°F (+50°C)
	ROHS Compliant	Yes
	Certification/Specification	CSA
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	120ft
	Package Quantity (Metric)	36.6m
	Customs Number(Schedule B)	3925900000