

181-15106

Article Number: 181-15106

Description: Slotted Cable and Wiring Duct, 1.5" x 1", Non-Adhesive, PVC, White, 30ft/box



Base Data	Local Order Number	181-15106
	Type	SL1.5X1
	Color	White (WH)
	Features and benefits	<ul style="list-style-type: none"> • Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.
	Quantity Per	box
	Product Description	Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a wider opening is required. The lower score line allows the sidewall to be smoothly cut for joints and "T's".
	Technical Description	Non-Adhesive
	Short Description	Slotted Cable and Wiring Duct, 1.5" x 1", Non-Adhesive, PVC, White, 30ft/box
	Product Dimensions	Length L (Imperial)
Length L (Metric)		1.83m
Width W (Imperial)		1.5"
Width W (Metric)		38.1mm
Width W2 (Imperial)		1.5"
Width W2 (Metric)		38.1mm
Width W3 (Imperial)		0.4"
Width W3 (Metric)		10.2mm
Width W4 (imperial)		1.0"
Width W4 (metric)		25.4mm
Width W5 (imperial)		0.75"
Width W5 (metric)		19.1mm

181-15106



Product Dimensions	Height H (Imperial)	1.06"
	Height H (Metric)	26.9mm
	Mounting Hole Centers (Imperial)	4.0"
Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	Self-Extinguishing
	Operating Temperature	+122°F (+50°C)
	ROHS Compliant	Yes
	Certification/Specification	UL
UL Recognized (US)	Yes	
Logistic and Packaging		
	Package Quantity (Imperial)	30.0ft
	Package Quantity (Metric)	9.1m
	Customs Number(Schedule B)	3925900000