

181-23002



Article Number: 181-23002

Description: Solid Cable and Wiring Duct, 2" x 3", Non-Adhesive, PVC, White, 120 ft/carton

Base Data	Local Order Number	181-23002
	Type	SD2X3
	Color	White (WH)
	Features and benefits	<ul style="list-style-type: none"> <li>• A temporary film is applied to the covers to protect against scratches and is writable for identification during installation.</li> <li>• Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement.</li> <li>• Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off. (Covers to be purchased separately)</li> </ul>
	Quantity Per	carton
	Product Description	HellermannTyton's Pro-Duct, Solid Wall wiring duct efficiently routes and protects wire and cable. Solid Wall wiring duct it designed for straight wire runs where break outs are not required. Pro-Duct, Solid Wall wiring duct is manufactured from high impact, rigid PVC, comes in standard colors of white, gray and black, and is available in 6 foot lengths.
	Technical Description	Non-Adhesive
	Short Description	Solid Cable and Wiring Duct, 2" x 3", Non-Adhesive, PVC, White, 120 ft/carton
	Product Dimensions	Length L (Imperial)
Length L (Metric)		1.83m
Width W (Imperial)		2.0"
Width W (Metric)		50.8mm
Width W2 (Imperial)		2.0"
Width W2 (Metric)		50.8mm
Width W6 (imperial)		0.5"
Width W6 (metric)		12.7mm
Height H (Imperial)		3.07"
Height H (Metric)		77.90mm
Mounting Hole Centers (Imperial)		4.0"

181-23002



Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	Self-Extinguishing
	Operating Temperature	+122°F (+50°C)
	ROHS Compliant	Yes
	Certification/Specification	CSA
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	120ft
	Package Quantity (Metric)	36.6m
	Customs Number(Schedule B)	3925900000