

181-23056



Article Number: 181-23056

Description: Solid Cable and Wiring Duct, 3" x 5", Non-Adhesive, PVC, Intrinsic Blue, 120 ft/carton



Base Data	Local Order Number	181-23056
	Type	SD3X5
	Color	Blue (BU)
	Features and benefits	<ul style="list-style-type: none"> <li>• Solid wall construction provides excellent coverage to keep wires and cables clean.</li> <li>• Durable material protects wires and cables from damage, with long-lasting performance.</li> <li>• Available standard color options to complement or contrast in light and dark environments.</li> <li>• Optional covers enhance protection and appearance.</li> </ul>
	Quantity Per	carton
	Product Description	HellermannTyton's Pro-Duct solid wall wiring duct efficiently routes and protects wires and cables. Solid wall wiring duct is designed for straight wire runs where breakouts are not required. Pro-Duct solid wall wiring duct is manufactured from high-impact, rigid PVC, and is available in 6-foot lengths in standard colors of white, gray and black.
	Short Description	Solid Cable and Wiring Duct, 3" x 5", Non-Adhesive, PVC, Intrinsic Blue, 120 ft/carton
	Product Dimensions	Length L (Imperial)
Length L (Metric)		1.83m
Width W (Imperial)		3.0"
Width W (Metric)		76.2mm
Width W2 (Imperial)		3.0"
Width W2 (Metric)		76.2mm
Width W6 (imperial)		1.0"
Width W6 (metric)		25.4mm
Height H (Imperial)		5.06"
Height H (Metric)		128.50mm
Mounting Hole Centers (Imperial)		4.0"

181-23056



Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	Self-Extinguishing
	Operating Temperature	+122°F (+50°C)
	ROHS Compliant	Yes
	Certification/Specification	UL
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	120ft
	Package Quantity (Metric)	36.6m