

181-35001

HellermannTyton



Article Number: 181-35001

Description: Slotted Cable and Wiring Duct, 3" x 5", Non-Adhesive, PVC, Black, 30 ft/ctn

| | | |
|--------------------|-----------------------|---|
| Base Data | | |
| | Local Order Number | 181-35001 |
| | Type | SL3X5 |
| | Color | Black (BK) |
| | Features and benefits | <ul style="list-style-type: none"> • Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection. |
| | Quantity Per | box |
| | Product Description | Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a wider opening is required. The lower score line allows the sidewall to be smoothly cut for joints and "T's". |
| | Technical Description | Non-Adhesive |
| | Short Description | Slotted Cable and Wiring Duct, 3" x 5", Non-Adhesive, PVC, Black, 30 ft/ctn |
| Product Dimensions | | |
| | Length L (Imperial) | 6.0ft |
| | Length L (Metric) | 1.83m |
| | Width W (Imperial) | 3.0" |
| | Width W (Metric) | 76.2mm |
| | Width W2 (Imperial) | 3.0" |
| | Width W2 (Metric) | 76.2mm |
| | Width W3 (Imperial) | 0.4" |
| | Width W3 (Metric) | 10.2mm |
| | Width W4 (imperial) | 1.0" |
| | Width W4 (metric) | 25.4mm |
| | Width W5 (imperial) | 4.6" |
| | Width W5 (metric) | 116.8mm |

181-35001

HellermannTyton

| | | |
|-----------------------------|----------------------------------|-------------------------|
| Product Dimensions | Width W6 (imperial) | 1.0" |
| | Width W6 (metric) | 25.4mm |
| | Height H (Imperial) | 5.06" |
| | Height H (Metric) | 128.50mm |
| | Mounting Hole Centers (Imperial) | 4.0" |
| Material and Specifications | | |
| | Material | Polyvinylchloride (PVC) |
| | Material Shortcut | PVC |
| | Flammability | Self-Extinguishing |
| | Operating Temperature | +122°F (+50°C) |
| | ROHS Compliant | Yes |
| | Certification/Specification | CSA |
| | UL Recognized (US) | Yes |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 30ft |
| | Package Quantity (Metric) | 9.14m |
| | Customs Number(Schedule B) | 3925900000 |