

181-44009

HellermannTyton



Article Number: 181-44009

Description: Solid Cable and Wiring Duct, 4" x 4", Non-Adhesive, PVC, Gray, 120ft /carton

| | | |
|--------------------|----------------------------------|--|
| Base Data | | |
| | Local Order Number | 181-44009 |
| | Type | SD4X4 |
| | Color | Gray (GY) |
| | Features and benefits | <ul style="list-style-type: none"> • A temporary film is applied to the covers to protect against scratches and is writable for identification during installation. • Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement. • Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off. (Covers to be purchased separately) |
| | Quantity Per | carton |
| | Product Description | HellermannTyton's Pro-Duct, Solid Wall wiring duct efficiently routes and protects wire and cable. Solid Wall wiring duct it designed for straight wire runs where break outs are not required. Pro-Duct, Solid Wall wiring duct is manufactured from high impact, rigid PVC, comes in standard colors of white, gray and black, and is available in 6 foot lengths. |
| | Technical Description | Non-Adhesive |
| | Short Description | Solid Cable and Wiring Duct, 4" x 4", Non-Adhesive, PVC, Gray, 120ft /carton |
| Product Dimensions | | |
| | Length L (Imperial) | 6.0ft |
| | Length L (Metric) | 1.83m |
| | Width W (Imperial) | 4.0" |
| | Width W (Metric) | 101.6mm |
| | Width W2 (Imperial) | 4.0" |
| | Width W2 (Metric) | 101.6mm |
| | Width W6 (imperial) | 1.5" |
| | Width W6 (metric) | 38.1mm |
| | Height H (Imperial) | 4.07" |
| | Height H (Metric) | 103.40mm |
| | Mounting Hole Centers (Imperial) | 4.0" |

181-44009



| | | |
|-----------------------------|-----------------------------|-------------------------|
| Material and Specifications | | |
| | Material | Polyvinylchloride (PVC) |
| | Material Shortcut | PVC |
| | Flammability | Self-Extinguishing |
| | Operating Temperature | +122°F (+50°C) |
| | ROHS Compliant | Yes |
| | Certification/Specification | UL |
| | UL Recognized (US) | Yes |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 120ft |
| | Package Quantity (Metric) | 36.6m |
| | Customs Number(Schedule B) | 3925900000 |