

184-12004

HellermannTyton



Article Number: 184-12004

Description: Slotted Cable and Wiring Duct, High-Density, 1" x 2", Adhesive, PVC, White, 120 ft/carton

| | | |
|--------------------|-----------------------|---|
| Base Data | | |
| | Local Order Number | 184-12004 |
| | Type | SLHDA1X2 |
| | Color | White (WH) |
| | Features and benefits | <ul style="list-style-type: none"> • Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance. • Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation. • Mounting holes are uniform in size to the solid and slotted wall duct, but are offered every 2 inches to accommodate compact designs and ease installation. |
| | Quantity Per | carton |
| | Product Description | Pro-Duct high density, slotted wall, wiring duct features narrow fingers, equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated. |
| | Technical Description | Adhesive |
| | Short Description | Slotted Cable and Wiring Duct, High-Density, 1" x 2", Adhesive, PVC, White, 120 ft/carton |
| Product Dimensions | | |
| | Length L (Imperial) | 6.0ft |
| | Length L (Metric) | 1.83m |
| | Width W (Imperial) | 1.0" |
| | Width W (Metric) | 25.4mm |
| | Width W2 (Imperial) | 1.0" |
| | Width W2 (Metric) | 25.4mm |
| | Width W3 (Imperial) | 0.16" |
| | Width W3 (Metric) | 4.1mm |
| | Width W4 (imperial) | 0.4" |
| | Width W4 (metric) | 10.2mm |
| | Width W5 (imperial) | 1.62" |
| | Width W5 (metric) | 41.1mm |

184-12004



| | | |
|-----------------------------|----------------------------------|-------------------------|
| Product Dimensions | Height H (Imperial) | 2.07" |
| | Height H (Metric) | 52.60mm |
| | Mounting Hole Centers (Imperial) | 2.0" |
| Material and Specifications | | |
| | Material | Polyvinylchloride (PVC) |
| | Material Shortcut | PVC |
| | Flammability | Self-Extinguishing |
| | Operating Temperature | +122°F (+50°C) |
| | ROHS Compliant | Yes |
| | Certification/Specification | CSA |
| | UL Recognized (US) | Yes |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 120ft |
| | Package Quantity (Metric) | 36.6m |