

184-15214



Article Number: 184-15214

Description: Slotted Cable and Wiring Duct, High-Density, 1.5" x 2", Non-Adhesive, PVC, Black, 30ft/box



|                    |                       |   |
|--------------------|-----------------------|---|
| Base Data          |                       |   |
|                    | Local Order Number    | 184-15214   |
|                    | Type                  | SLHD1.5X2   |
|                    | Color                 | Black (BK)  |
|                    | Features and benefits | <ul style="list-style-type: none"> <li>• Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.</li> <li>• Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.</li> <li>• Mounting holes are uniform in size to the solid and slotted wall duct, but are offered every 2 inches to accommodate compact designs and ease installation.</li> </ul> |
|                    | Quantity Per          | box   |
|                    | Product Description   | Pro-Duct high density, slotted wiring duct features narrow fingers, a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.   |
|                    | Technical Description | Non-Adhesive  |
|                    | Short Description     | Slotted Cable and Wiring Duct, High-Density, 1.5" x 2", Non-Adhesive, PVC, Black, 30ft/box  |
| Product Dimensions |                       |   |
|                    | Length L (Imperial)   | 6.0ft   |
|                    | Length L (Metric)     | 1.83m   |
|                    | Width W (Imperial)    | 1.5"  |
|                    | Width W (Metric)      | 38.1mm  |
|                    | Width W2 (Imperial)   | 1.5"  |
|                    | Width W2 (Metric)     | 38.1mm  |
|                    | Width W3 (Imperial)   | 0.16"   |
|                    | Width W3 (Metric)     | 4.1mm   |
|                    | Width W4 (imperial)   | 0.4"  |
|                    | Width W4 (metric)     | 10.2mm  |
|                    | Width W5 (imperial)   | 1.60"   |
|                    | Width W5 (metric)     | 40.6mm  |

184-15214

**HellermannTyton**

|                             |                                  |                         |
|-----------------------------|----------------------------------|-------------------------|
| Product Dimensions          | Height H (Imperial)              | 2.07"                   |
|                             | Height H (Metric)                | 52.6mm                  |
|                             | Mounting Hole Centers (Imperial) | 2.0"                    |
| Material and Specifications |                                  |                         |
|                             | Material                         | Polyvinylchloride (PVC) |
|                             | Material Shortcut                | PVC                     |
|                             | Flammability                     | Self-Extinguishing      |
|                             | Operating Temperature            | +122°F (+50°C)          |
|                             | ROHS Compliant                   | Yes                     |
|                             | Certification/Specification      | CSA                     |
|                             | UL Recognized (US)               | Yes                     |
| Logistic and Packaging      |                                  |                         |
|                             | Package Quantity (Imperial)      | 30.0ft                  |
|                             | Package Quantity (Metric)        | 9.1m                    |