

Article Number: 184-22002

Description: Slotted Cable and Wiring Duct, High-Density, 2" x 2",
Adhesive, PVC, White, 30ft/box



Base Data	
Local Order Number	184-22002
Type	SLHDA2X2
Color	White (WH)
Features and benefits	<ul style="list-style-type: none"> • Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance. • Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation. • Mounting holes are uniform in size to the solid and slotted wall duct, but are offered every 2 inches to accommodate compact designs and ease installation.
Quantity Per	box
Product Description	Pro-Duct high density, slotted wall, wiring duct features narrow fingers, equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.
Technical Description	Adhesive
Short Description	Slotted Cable and Wiring Duct, High-Density, 2" x 2", Adhesive, PVC, White, 30ft/box
Product Dimensions	
Length L (Imperial)	6.0ft
Length L (Metric)	1.83m
Width W (Imperial)	2.0"
Width W (Metric)	50.8mm
Width W2 (Imperial)	2.0"
Width W2 (Metric)	50.8mm
Width W3 (Imperial)	0.16"
Width W3 (Metric)	4.1mm
Width W4 (imperial)	0.4"
Width W4 (metric)	10.2mm
Width W5 (imperial)	1.6"
Width W5 (metric)	40.6mm

184-22002



Product Dimensions	Width W6 (imperial)	0.5"
	Width W6 (metric)	12.7mm
	Height H (Imperial)	2.07"
	Height H (Metric)	52.6mm
	Mounting Hole Centers (Imperial)	2.0"
Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	Self-Extinguishing
	Operating Temperature	+122°F (+50°C)
	ROHS Compliant	Yes
	Certification/Specification	CSA
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	30.0ft
	Package Quantity (Metric)	9.1m
	Customs Number(Schedule B)	3925900000