

190-00147

# HellermannTyton



Article Number: 190-00147

Description: Snapper Hose Clamp, 1.29"–1.58" Bundle Diameter, POM, White, 500/pkg

## Base Data

Local Order Number	SNP3310H4
Type	SNP33
Color	White (WH)
Features and benefits	<ul style="list-style-type: none"> <li>• Designed for quick, ratcheted installation and can be released and reused.</li> <li>• Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.</li> </ul>
Quantity Per	bag
Product Description	<p>Snapper Hose Clamps are lightweight and corrosion-resistant. Manufactured from high-performance thermoplastic materials selected to work well in a variety of diverse environments.</p> <p>A quick ratchet closure provides for reduced assembly line time and allows for application after connection of the hose. Release is achieved by initiating opposed lateral movement of the ratchet ends.</p> <p>Heat stabilized materials are available for high-temperature, motor, and under-hood applications. Snappers are also stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils, and greases.</p> <p>The Snapper is available in 32 standard sizes ranging from 1/4" to 4-1/2" ID. Snappers are manufactured in white polyacetal and black polyamide 6.6 glass filled impact modified heat stabilized material. Custom designed and different colored or shaped Snappers are available based upon applications and volume requirements.</p>
Short Description	Snapper Hose Clamp, 1.29"–1.58" Bundle Diameter, POM, White, 500/pkg

## Product Dimensions

Fixation Method	Plug-in mounting
Variant	Closed
Width W2 (Imperial)	0.291"
Width W2 (Metric)	7.39mm
Diameter Min. (Imperial)	1.291"
Diameter Min. (Metric)	32.79mm
Diameter Max. (Imperial)	1.582"
Diameter Max. (Metric)	40.18mm
Wall Thickness WT (Imperial)	.067"

190-00147

**HellermannTyton**

Product Dimensions	Wall Thickness WT (Metric)	1.7mm
Material and Specifications		
	Material	Polyacetal (POM)
	Material Shortcut	POM
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500
	Customs Number(Schedule B)	3926909987