

190-00190

HellermannTyton



Article Number: 190-00190

Description: Snapper Hose Clamp, .45"–.51" Bundle Diameter, POM, White, 1000/pkg

Base Data

Local Order Number	SNP610M4
Type	SNP6
Color	White (WH)
Features and benefits	<ul style="list-style-type: none"> • Designed for quick, ratcheted installation and can be released and reused. • Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.
Quantity Per	bag
Product Description	<p>Snapper Hose Clamps are lightweight and corrosion-resistant. Manufactured from high-performance thermoplastic materials selected to work well in a variety of diverse environments.</p> <p>A quick ratchet closure provides for reduced assembly line time and allows for application after connection of the hose. Release is achieved by initiating opposed lateral movement of the ratchet ends.</p> <p>Heat stabilized materials are available for high-temperature, motor, and under-hood applications. Snappers are also stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils, and greases.</p> <p>The Snapper is available in 32 standard sizes ranging from 1/4" to 4-1/2" ID. Snappers are manufactured in white polyacetal and black polyamide 6.6 glass filled impact modified heat stabilized material. Custom designed and different colored or shaped Snappers are available based upon applications and volume requirements.</p>
Short Description	Snapper Hose Clamp, .45"–.51" Bundle Diameter, POM, White, 1000/pkg

Product Dimensions

Fixation Method	Plug-in mounting
Variant	Closed
Width W2 (Imperial)	0.232"
Width W2 (Metric)	5.89mm
Bundle Diameter Min. (Imperial)	0.47"
Bundle Diameter Min. (Metric)	12.0mm
Bundle Diameter Max. (Imperial)	0.54"
Bundle Diameter Max. (Metric)	13.7mm
Diameter Min. (Imperial)	0.454"

190-00190

HellermannTyton

Product Dimensions	Diameter Min. (Metric)	11.53mm
	Diameter Max. (Imperial)	0.513"
	Diameter Max. (Metric)	13.03mm
	Wall Thickness WT (Imperial)	.069"
	Wall Thickness WT (Metric)	1.8mm
Material and Specifications		
	Material	Polyacetal (POM)
	Material Shortcut	POM
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1000
	Package Quantity (Metric)	1000
	Customs Number(Schedule B)	3926909987