

190-00209

# HellermannTyton

Article Number: 190-00209



Description: Snapper Hose Clamp, 2.63"—3.15" Bundle Diameter, PA66GF13, Black, 100/pkg

Base Data		
	Local Order Number	SNP70GHS0C2
	Type	SNP70
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Designed for quick, ratcheted installation and can be released and reused.</li> <li>• Heat stabilized material is suitable for high temperature applications.</li> </ul>
	Quantity Per	bag
	Product Description	<p>Snapper Hose Clamps are lightweight and corrosion-resistant. Manufactured from high-performance thermoplastic materials selected to work well in a variety of diverse environments.</p> <p>A quick ratchet closure provides for reduced assembly line time and allows for application after connection of the hose. Release is achieved by initiating opposed lateral movement of the ratchet ends.</p> <p>Heat stabilized materials are available for high-temperature, motor, and under-hood applications. Snappers are also stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils, and greases.</p> <p>The Snapper is available in 32 standard sizes ranging from 1/4" to 4-1/2" ID. Snappers are manufactured in white polyacetal and black polyamide 6.6 glass filled impact modified heat stabilized material. Custom designed and different colored or shaped Snappers are available based upon applications and volume requirements.</p>
	Short Description	Snapper Hose Clamp, 2.63"—3.15" Bundle Diameter, PA66GF13, Black, 100/pkg
Product Dimensions		
	Fixation Method	Plug-in mounting
	Variant	Closed
	Width W2 (Imperial)	0.295"
	Width W2 (Metric)	7.49mm
	Diameter Min. (Imperial)	2.634"
	Diameter Min. (Metric)	66.9mm
	Diameter Max. (Imperial)	3.146"
	Diameter Max. (Metric)	79.91mm
	Wall Thickness WT (Imperial)	.078"

190-00209



Product Dimensions	Wall Thickness WT (Metric)	2.02mm
Material and Specifications		
	Material	Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13%)
	Material Shortcut	PA66GF13
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987