

250-63600

HellermannTyton



Article Number: 250-63600

Description: Power Rated Raceway Channel, 1.75", 6ft Long, PVC, Office White, 120 ft/carton

Base Data		
	Local Order Number	TSRP3FW-6A
	Type	TSRP3-6A
	Color	Office White (OEWH)
	Features and benefits	<ul style="list-style-type: none"> • Self-locking covers, provide taper resistant security, while the hidden positive latch permits quick re-entry access to power cables. • An integrated flexible hinge allows the raceway to endure numerous openings without stress cracking or discoloration. • Raceways and fittings are UL Listed for power up to 600 Volts and meet UL5A and CSA 22.2 Number 62-93 Standards, to insure compliance with local building codes. Raceway fittings incorporate a minimum 1" bend radius to meet TIA/EIA 568-B and 569-A standards.
	Quantity Per	carton
	Product Description	HellermannTyton provides a complete line of raceway and fittings to manage connectivity requirements from the telecommunications room to the work area. Each size of raceway offers numerous fittings, offered in electrical ivory, white or office white, including TIA/EIA-568-B compliant 1" bend radius accessories which help ensure consistent data transmission performance of Category 6A, 6 and 5e communications systems.
	Short Description	Power Rated Raceway Channel, 1.75", 6ft Long, PVC, Office White, 120 ft/carton
Product Dimensions		
	Length L (Imperial)	6.0ft
	Length L (Metric)	1.83m
	Width W (Imperial)	1.75"
	Width W (Metric)	44.45mm
	Height H (Imperial)	1.0"
	Height H (Metric)	25.40mm
Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	ROHS Compliant	Yes

250-63600



Material and Specifications	UL Listed (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	120ft
	Package Quantity (Metric)	36.6m
	Customs Number(Schedule B)	3925900000