

251-10109

Article Number: 251-10109

Description: Grommet, Panel Thickness 0.016"-0.051", PE, Natural, 82ft/pkg



Base Data	Local Order Number	FPA
	Type	G51PA
	Color	Natural (NA)
	Features and benefits	<ul style="list-style-type: none"> • Can be cut to length with scissors, eliminating waste and keeping stock to a minimum. • Available in 9 sizes, for thicknesses from .016" to .512", insuring proper fit.
	Quantity Per	reel
	Product Description	HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.
	Short Description	Grommet, Panel Thickness 0.016"-0.051", PE, Natural, 82ft/pkg
	Product Dimensions	Length L (Imperial)
Reel Length (imperial)		9.7ft
Variant		Open
Width W (Imperial)		0.154"
Width W (Metric)		3.9mm
Width W2 (Imperial)		0.059"
Width W2 (Metric)		1.5mm
Height H (Imperial)		0.169"
Height H (Metric)		4.3mm
Height H2 (Imperial)		0.106"
Height H2 (Metric)		2.7mm
Panel Thickness Max. (Imperial)		0.051"
Panel Thickness Max. (Metric)		1.30mm
Panel Thickness Min. (Imperial)		0.016"

251-10109



Product Dimensions	Panel Thickness Min. (Metric)	0.40mm
Material and Specifications		
	Material	Polyethylene (PE)
	Material Shortcut	PE
	Flammability	UL 94 HB
	Halogenfree	Yes
	Operating Temperature	-22°F to +176°F (-30°C to +80°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	82ft
	Package Quantity (Metric)	25m
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	reel
	Weight (Metric)	0.32kg